

Distansförlängning från vägg för armbågskontakt i metall.

Distansen innehåller rillor som kan användas som kabelgenomföringar vid utanpåliggande kabeldragning (se bilden till höger).



Material:
PETG
Polyetylentereftalatglykol (PETG).


Rengöring:
Distansen går att rengöra med alla förekommande rengöringsmedel.

Storlekar:
Distansen går att beställa i följande storlekar:

JCK20: B:80 H:245 D:10mm

JCK21: B:80 H:245 D:25mm

Hålbildsritning:




Rillor för kabelgenomföring

OBS.

Vid utomhusmontage ska den nedre rillan skäras bort i distansens nedre kant för att dränera bort eventuell fukt.

Assembly and installation.

1. Cut out the desired wire outlet in the elbow switch extension. A regular cutter can be used.
2. Remove the aluminum lid. For more information, refer to JCK 207 and JCK 108 product data sheets respectively.
3. Pass the electric wiring (12-24 V) through the wire outlet, and connect it to the connection terminal. (see image below)
4. Fixate the aluminum core and the distance with assembly and washers.
5. Place back the lid. For more information, refer to JCK 207 and JCK 108 product data sheets respectively.



Click [here](#) to go to the product Spacer for metal AK.